

# Elmasolvex® SE - Manual

Multiple-chamber technology for solvent and aqueous cleaning



*Elmasolvex® SE with wide range of accessories*

Can a classic be invented again?

- TÜV-certified explosion safety
- now with 4 cleaning chambers and one heating chamber (fine filter warm air technology)
- manual operation with latching in the working heights and above the media container positions
- service-friendly and easy-to-care for design
- maximum personnel safety due to connection of the machine to controlled exhaust air routing
- basket frame for five baskets, optional holder for circuit boards
- Wide range of practical accessories; see accessories catalogue

Process:  
Rotation process

Solvent cleaning:  
flashpoint from > 12 °C; e.g. WF pro, 3 x elma suprol pro, drying

Semi-aqueous combination process:  
e.g. Elma 1:9, demineralised water, 2 x elma suprol pro, drying  
or Elma 1:9, demineralised water, 2 x IPA, drying

Process and media



Rotation



Solvent



Aqueous



64 mm  
baskets



*Inserting basket frame*



*Connecting to exhaust air routing*



*Preselecting setting*



*Raising, lowering and closing*

